


SEE D6106-1
FOR LAMP
ASSY.

MOUNTED
IN LENS.
NO ADJ.
DS1



END OF DOC
DS2

MOUNTED
IN KEYS.
CHAR/STOP
DS3

SEARCH
DS4

SKIP
DS5

REF. SW. W.L.*325-2217
MOUNTED EXTERNALLY.
MECHANICAL INTERLOCK
DEPRESS AND RELEASE
ONE SWITCH AT A TIME.
SAME SWITCH, SHOWN
DEPRESSED.



REVISIONS	
REVISED: PER	E.C.*3217, F.S.S.
9-16-72	APP'D SKH
REVISED: PER	E.C.*3514 F.S.S.
2-8-73	APP'D SKH

COMPONENT	SIZE, TYPE	W.L. NO.	QTY.
C1	10μf 15V	300-3006	1
C2	.05μf 12V	300-1900	1
DS1, 2, 3, 4, 5	CM-6833	370-0015	5
SW1, 2, 3, 4, 5, 6, 7, 8	11SM1	325-2305	8

I.C. LOCATION	TYPE	W.L. NO.	TERM FOR ±0V	TERM FOR VCC +5VR	QTY.
L1, 2, 3	F9936	376-0026	7	14	2

WANG LABORATORIES INC.			
TEWKSBURY, MASS.			
MODEL NO.	DRAWN	F.S.S. 2-8-72	APP'D 3/17/72
1200	CHECKED		APP.
TITLE SCHEMATIC LOGIBLOC RIGHT KEYBOARD FOR MODEL 1200			
W.O. NO.	DWG. NO.	C 6014-1	REV. 2

1-71093